

LC Thomsen Centrifugal Pump

Mfg: Thomsen

Model: 4

Stock No. OIP087.

Serial No. 3A 6661

LC Thomsen Centrifugal Pump. Model: 4. S/N: 3A 6661. Pump capacity: 60 gpm @ 47 TDH. Baldor Industrial Motor, 1 hp, 3450 rpm, 208-230/460 V, 3.4-3.2/1.6 amps, 60 Hz, 3 phase. Thomsen pumps are manufactured from type 316 stainless steel and polished to a sanitary finish. Backplates incorporate a ceramic wear ring to reduce replacement costs. Inlet: 1-1/2 in. dia. S-line fitting. Outlets: 1-1/2 in. dia. FNPT. Overall dimensions: 17-1/4 in. L x 6-1/2 in. W x 14 in. H.



