

## Waukesha 60 Positive Displacement Pump

Mfg: Waukesha

Model: 60

Stock No. OIP105.

Serial No. 2785 SS

Waukesha 60 Positive Displacement Pump. Model: 60. S/N: 2785 SS. 3-A Sanitary rated. Pumping capacity (min/max): 12/60 gpm. Displacement per revolution: 0.153 gal. Nominal capacity: 90 gpm. Maximum rpm: 600. Seal option: o-ring. U.S. Motor, 7-1/2 hp, 1800 rpm, 23/460 V, 24.5/12.25 amps, 60 Hz, 3 phase. U.S. Varidrive Module, 80 rpm (min), 395 rpm (max). Typical product application: (beverage), fruit concentrates, fruit drinks, wine, (confectionery) syrups, cream fillings, chocolate, (dairy) cream, milk, butter. Inlets/outlets: 2-1/2 in. dia. S-line fittings. Overall dimensions: 65 in. L x 20 in. W x 32-1/2 in. H.



