

1997 Ltt Goulds Pumps Centrifugal 3196 STX Series

Mfg: Ltt Goulds Pumps

Model: 3196 STX

Stock No. OIP126.

Serial No. 711E662

1997 Ltt Goulds Pumps Centrifugal 3196 STX Series. Model: 3196 STX. S/N: 711E662. Size: 1x1.5-8. Capacity: 90 gpm @ 55 head feet (21.7 psi using specific gravity of water = 1). Least Displacement per Revolution: .057 gal. Impeller diameter: 8 in. Baldor Industrial Motor, 2 hp, 1725 rpm, 208-230/460 V, 6.5-6.2/3.1 amps, 60 Hz, 3 phase. STX units are constructed of Novolac Epoxy, which resists most acids, alkalines and solvents for long service life. Standard features include catch basins, grout holes and inserts of 304 stainless steel. It continues to be recognized as a workhorse in chemical, petrochemical, pulp and paper, primary metals, food and beverage, and general-industry processes. Inlet: (1) 1 ½ in. dia. flanged port. Outlet: (1) 1 in. dia. flanged port. Overall dimensions: 1 ft. 6 in. L x 9 in. W x 1 ft. H.



