

Croll-Reynolds Multiple Nozzle Thermocompressor

Mfg: Croll-Reynolds

Model: M12-T

Stock No.: 2500.PF1aB

Serial No.: 52311-1, and 52311-2

(2) Croll-Reynolds Multiple Nozzle Thermocompressor. Model: M12-T. SN: 52311-1, and 52311-2. Material of construction: 316 SS body and steel cover. Number of Nozzles: (7). Maximum pressure: 40 psi Inlets: (1) 4 in. dia. port with 9 in. flange and (8) 3/4 in. bolt holes (Motive fluid). (1) 12 in. port with a 19 in. flange and (12) 1 in. bolt holes (Suction). Outlet: (1) 12 in. port with a 19 in. flange and (12) 1 in. bolt holes. Overall dimensions: 8 ft. L x 1 ft. 5 in. W x 1 ft. 9 in. H. (ACN6 ea.)





