

Howden WRV 204/165 Rotary Screw Compressor

Mfg: Howden

Model: MK4B/WRV204/16526/1400

Stock No: PMI454.a7a

Serial No: JH1839

Howden WRV 204/165 Rotary Screw Compressor. Model: MK4B/WRV204/16526/1400. S/N: JH1839. Vi setting: 2.6. Displacement: 853 cfm. Rotor diameter: 204 mm. Rotor speed: 4,500 rpm maximum, 1,500 minimum. Maximum inlet pressure: 75 psi. Maximum outlet pressure: 260 psi. Connections: 8 in. suction and 5 in. discharge. Approximate weight: 1,874 lbs. Overall dimensions: 4 ft. 9 in. L x 2 ft. 2 in. W x 2 ft. 3 in. H.





