

Sundyne Maso / Sine SPS-3 Positive Displacement Pump

Mfg: Sundyne Maso / Sine

Model: SPS-3

Stock No: 35.R458-B.10

Serial No: 10108SP-002

Sundyne Maso / Sine SPS-3 Positive Displacement Pump. Model: SPS-3. S/N: 10108SP-002. ID: 71. Flow rate for new pump is 75 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Seal option: lip seals. Patented design assures powerful suction for high viscosity applications. Constant volumetric displacement creates a smooth and consistent flow. One rotor, one shaft, and one seal assembly equate to simple, economical maintenance. Electrical motor, 5 hp, 1750 rpm, 208-230/460 V, 13.8-13.4/6.7 amps, 60 Hz, 3 phase. Ratio: 9:1. Final rpm: 194. Inlets/outlets: (2) 3 in. dia. S-line fittings. Overall dimensions: 4 ft. 2-1/2 in. L x 1 ft. 2 in. W x 1 ft. 7 in. H. (ACN75a).









