Reliance Electric Agitator Drive	
Mfg: Reliance	Model:
Stock No. RA-30.4a	Serial No. 448146-KT

Reliance Electric Agitator Drive. S/N: 448146-KT. Gear driven for maximum torque output. Shaft dimensions: 3/4 in. dia. x 2-1/2 in. L. Reliance Electric Motor, 3/4 Hp, 1725/860 rpm, 230/460 Volts, 1.35/0.67 Amps, 60 Hz, 3 phase. Motor Drive, 35/17.5 rpm (final). Mounting base has a 10 in. dia. flange with (4) 1/2 in. dia. attachment holes at a center-to-center distance of 9 in. Overall dimensions: 22 in. L x 11 in. W x 11-1/2 in. H.







