

Cherry-Burrell Jacketed Rectangular Tank- 1300 Gallons	
Mfg: Cherry-Burrell	Model: GRW
Stock No: RAAF136.36	Serial No: 12-71-2669

Cherry-Burrell Jacketed Rectangular Tank. Model GRW. S/N: 12-71-2669. Approximate capacity: 1300 gallons. Includes a full length, floor mounted 7 in. dia. impeller on a 1 in. dia. impeller shaft, (1) 5 in. dia. sight glass with a 3-step access ladder for view. (1) 4 in. dia. sprayball for CIP cleaning. Baldor Electric motor: ¾ Hp, 1725 rpm, 208-230/460 volts, 3.2-3.0/1.5 amps, 60 Hz, 3 phase. Perfection Electric Inc. Model: SA11130S. Serial no. 32293H980. motor drive: 40 to 1 ratio. REOTEMP gauge dial. Inlets/outlets: (2) 1-3/8 in. MNPT. (1) 2-1/8 in. MNPT. (1) 3 in. s-line. (1) 2 in. s-line. (1) 1-1/2 in. ACME. (1) 3 in. dia. ventilator. (1) 20 in. x 16 in. manway. Inside dimensions: 5 ft. 3-1/4 in. L. x 4 ft. 9 in. W. x 6 ft. 3-1/2 in. Straight wall. Overall dimensions: 7 ft. 4-1/4 in. L. x 5 ft. 7 in. W. x 9 ft. 7 in. H.(ACN355).







