

York 6-Cylinder Reciprocating Compressor- 75 HP

Mfg: York

Model: RW64-717A

Stock No. RAAF173.2

Serial No. HY0433288081202

York R-Series 6-Cylinder Reciprocating Compressor- 75 HP. Model: RW64-717A. S/N: HY0433288081202. Nat'l Bd: 53205. Test pressure hi/lo: 450/330 psig. Refrigerant: R-717 ammonia. Features: water-cooled heads, 4.5 in. stroke. Marathon Electric Motor, 75 hp, 1185 rpm, 230/460 V, 196/98 amps, 60 Hz, 3 phase. (2) Receiving tanks: 50 Gallon. Magnetrol Liquid Level Control. Overall dimensions: 82 in. L x 72 in. W x 88 in. H.

Model: RW64-717A

R: R-Series

W: Water Cooled Heads

6: 6-Cylinders

4: 4.5 in. Stroke

717: R-717 Ammonia Refrigerant

A: 4.5 in. Stroke, compressor design series.







