

Viking Internal Gear Pump

Mfg: Viking Pump Inc.

Model: H432

Stock No: RB-122.1

Serial No: 1021034

Viking Internal Gear Pump. Model: H432. S/N: 1021034. Flow rate for new pump is 10 gpm with required horsepower and rpms. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Maximum pump speed is 1200 rpm. Maximum flow rate is 10 gpm at 1200 rpm. Maximum pressure is 100 psi. Pump internals are cast iron with a mechanical seal. Baldor Industrial Motor, 1 hp, 1725 rpm, 208-230/460 V, 3.8-3.4/1.7 amps, 60 Hz, 3 phase, 143T frame. Motor pulley: 3 in. Pump pulley: 6 in. Current final rpms at pump is 863. Inlet/outlet: (2) 1 in. FNPT. Overall dimensions: 2 ft. L x 1 ft. 3 in. W x 9 in. H.



