
Viking Internal Gear Pump		
Mfg: Viking Pump Inc.	Model: H432	
Stock No: RB-127.1	Serial No: 2040204	

Viking Internal Gear Pump. Model: H432. S/N:2040204. Flow rate for new pump is 10 gpm with required horsepower and rpms. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Maximum pump speed is 1200 rpm. Maximum flow rate is 10 gpm at 1200 rpm. Maximum pressure is 100 psi. Pump internals are cast iron with a mechanical seal. U.S. Electric Motor, 1 hp, 1755 rpm, 230/460 V, 3.8/1.9 amps, 60 Hz, 3 phase, 143T frame. Motor pulley: 3 in. Pump Pulley: 6 in. Current final rpms at pump is 878. Inlet/outlet: (2) 1 in. FNPT. Overall dimensions: 2 ft. L x 1 ft. 3 in. W x 10 in. H.















	PH BRA TYPE ENCL RPM DUTY: CONT	HZ SF 1.1
Team Reality (1) Reality (1)	MARK AMPS U.S. ELECTRICAL MORE MUSICION STRATEGING	and