

Trane Air Cooled Condensing Unit- 100 Ton

Mfg: Trane

Model: CGAA-10001-RA

Stock No. 80.RB259

Serial No. L77J04142.2

Trane Air Cooled Condensing Unit- 100 Ton. Model CGAA-10001-RA. S/N L77J04142. Refrigerant: R-22. Test pressure (hi/lo): 450/300 psig. Power supply: 460 V. (2) Remanufactured Trane 6-Cylinder Reciprocating Compressors, Models: CRHF500C4A0R2J0C0 and CRHR5004HAT, S/N's: N98L002297M and 466033-55, power supply: 460 V, 396 LRA, 60 Hz, 3 phase. (3) Fan Motors, 7.5 hp, 11 FLA, 60 Hz, 3 phase. Inlets: (1) 2-1/2 in. dia. copper tube suction port. Outlets: (1) 1-1/2 in. dia. copper tube discharge. Overall dimensions: 254 in. L x 77 in. W x 76 in. H.











