

Durco Centrifugal Pump

Mfg: Durco

Model:

Stock No. RB-467.1

Serial No. 187678

Durco Centrifugal Pump. S/N: 187678. Size: 1-1/2 x1-6/60. Maximum design pressure: 275 psi @ 100 °F. Alloy: D4. Reliance Electric Motor, 1.5 hp, 1725 rpm, 208-230/460 V, 5.6-5.6/2.8 amps, 60 Hz, 3 phase. Inlets: 1-1/2 in. dia. 125 lb. ANSI flange. Outlets: (1) 1 in. dia. 125 lb. ANSI flange. Overall dimensions: 35 in. L x 13-1/2 in. W x 17-1/2 in. H.

