

Chester Jensen Falling Film Plate Chiller – 60 Tons

Mfg: Chester Jensen

Model:

Stock No: RBFM269a.22

Serial No:

Chester Jensen Falling Film Plate Chiller. Cooling capacity: 60 tons at 96 gpm for a 26°F suction with a 15° TD. (3) plates with 36 corrugations each. Total cooling section area: 128.25 sq. ft. Plate dimensions: 4 ft. 1 in. L. x 3 ft. 9-1/2 in. W. MAWP: 200 psi @ 200 °F. Shell thickness: 0.45 in. Head thickness: 0.45 in. Collecting tank: 100 gallons. Inside-straight wall dimensions: 5 ft. 5 in. L. x 2 ft. 4 in. W. x 1 ft. 5 in. H. Inlets: (2) 2-1/2 in. dia. port. Outlets: (1) 2 in. dia NPT fitting. (1) 3 in. dia. NPT fitting. Overall dimensions: 8 ft. L. x 2 ft. 8-1/2 in. W. x 6 ft. 9-1/2 in. H.

Plate S/N's: 27702, 27703, 27701. Plate Nat'l Bd's: 3860, 3861, 3869.





