

GEA Ahlborn Plate Heat Exchanger - 1,117 Sq. Ft.

Mfg: GEA Ahlborn

Model:

Stock No: RCJF150.37a

Serial No: 185 / 235

1991 GEA Ahlborn plate heat exchanger skid. Type: N40. Serial No: 185 / 235. Total amount of plates: 195 in 3 sections: (1) 52 plates. 2) 69 plates. 3) 74 plates.) Heat transfer area: approx. 1,117 sq. ft. Maximum working pressure: 145 psig., Maximum working temperature: 212°F. Skid mounted items include: Reliance motor: ID # P21G1048F, frame: 215TO, 10 hp, 3485 rpm, 25.4 / 12.7 amps, 230 / 460V, 3 phase, 60 Hz. Baldor motor: Cat no. CM359T, spec 35A002R932HI, S/N: FO308203568, 3 hp, 3460 rpm, 7.8-7 / 4.3-7 amps, 208-230 / 460 V, 3 phase, 60 Hz. Inlets: S-line (2) 4 in. and (1) 3 in., Outlets: S-line (2) 3 in. and (1) 2-1/2 in. Overall dimensions: 10 ft. ½ in. L x 5 ft. 4 in. W. x 7 ft. 4 in. H.





