

## 1996 Mycom 250VLD Rotary Screw Compressor Package

Mfg: Mycom

Model: 250VLD

Stock No: RCJF1520.22a

Serial No: 2515114

1996 Mycom 250VLD Rotary Screw Compressor Package. Model: 250VLD. Serial no: 2515114. Sales order no. SU650. Maximum speed: 3600. Refrigerant: last used with R-717 (ammonia). Variable Vi: 2.6 to 5.8. Displacement: 1,670 cfm. Mycom oil separator: Serial no: RV 1629. National board no: 1597. Year built: 1996. MAWP: 300 psi at 650 °F. MDMT: -20 °F at 300 psi. Head thickness: 0.394. Shell thickness: 0.375. Corrosion allowance: 0. Oil separator dimensions: 11 ft. 11 in. straight wall x 2 ft. 10 in. dia. Viking pump. Model and serial number unavailable. Baldor motor: 5 Hp, 1160 Rpm, 208-230/460 V, 17-15.8/7.9 A, 60 Hz, 3 Phase. Inlets/outlets: (1) 1 ft. 1 in. outer flange dia. with (12) 7/8 in. mounting holes. (1) 1 ft. 5 in. outer flange dia. with (12) 3/4 in. mounting holes. (1) 3/4 in. FNPT. Overall dimensions: 14 ft. 8 in. L x 5 ft. W x 7 ft. 7 in. H.



