

Tri Clover PR300 Pump

Mfg: Tri Clover

Model: PR300-4-TC1-4-ST-S

Stock No: RCJF1602.15

Serial No: T7122J

Tri-Clover Rotary Pump. Model: PR300-4-TC1-4-ST-S. S/N: T7122J. Flow rate for new pump is 300 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. (2) 7-3/4 in. rotors. General Electric motor: 20 HP, 1770 RPM, 200-230/460 V, 49.2/24.6 A, 60 Hz, 3 Phase. (2) 6 in. dia. flanges. (8) 7/8 in. dia. mounting holes. 3-5/8 in. adjacent, 9-1/2 in. opposite. Overall dimensions: 6 ft. 1-1/2 in. L x 1 ft. 9 in. W x 2 ft. 2 in. H.(GJ).







