

Tri-Clover Positive Displacement Pump

Mfg: Tri-Clover

Model:

Stock No: RCJF1632F

Serial No:

Tri-Clover Positive Displacement Pump. Sterling Electric motor: 20 Hp, 1750 Rpm, 230/460 V, 48.3/24.15 A, 60 Hz, 3 Phase. Sterling Electric drive: 20.0 input Hp, 1800/238 Rpm in/out, 7.1 ratio. Overall dimensions: 5 ft. L x 1 ft. 10 in. W x 2 ft. 1-1/4 in. H.





		STERLING ELECTRIC, INC. <small>499-2418-2</small>		
HP 20	MODEL NO. E80204PCA	ENCL. TEFC		
POLE 4	MAX. AMB. 40 °C	VOLTS 230/460	HZ 60	
FRAME 256TC	TIME RATING CONT.	AMP. 48.3/24.15		
INS. CLASS F	DATE CODE 0993	RPM 1750		
NEMA DES. B	P.F. 0.90	SER. NO. 020121		
NEMA CODE G	NOM. FL. 90.2	BRG. D.E. 5310LL		
S.F. 1.15	EFF. 3/4 L. 90.2	NO. 0.0.E. 5233LL		
USABLE ON 208V		AMP.		
STERLI-SEAL				
MANUFACTURED BY STERLING ELECTRIC, INC.				
<small>INDIANAPOLIS, IN IRVINE, CA HAMILTON, ONT.</small>				

MEMBER OF STERLING ELECTRIC, INC. <small>499-2368-2</small>	
MODEL NO. SH06E 210 20 230	
INPUT RPM 1800	RATIO 7.1
OUTPUT RPM 230	INSUL. RP 20.0
CLASS I	AGMA OIL GRADE 6EP
IRVINE, CA	INDIANAPOLIS, IN HAMILTON, ONT.
UNIT SHIPPED WITH OIL	