

Tri-Clover Positive Displacement Pump

Mfg: Tri-Clover

Model: PR125-3-UC4-ST-S

Stock No: RCJF1632G

Serial No: X1634

Tri-Clover Positive Displacement Pump. Model: PR125-3-UC4-ST-S. S/N: X1634. Flow rate for new pump is 120 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. No rotors. Pulleys dia: 5 in. driver, 1 ft. 2 in. driven. Teco Electric and Machine Company, LTD. motor: 5 Hp, 1150 Rpm, 230/460 V, 14/7 A, 60 Hz, 3 Phase. Overall dimensions: 2 ft. 2 in. L x 1 ft. 11 in. W x 3 ft. 5-3/4 in. H.



