

Tri-Clover Positive Displacement Pump

Mfg: Tri-Clover

Model: PP125-3M-UH4-SL-S

Stock No: RCJF1633A

Serial No: 104613-04

Tri-Clover Positive Displacement Pump. Model: PP125-3M-UH4-SL-S. S/N: 104613-04. Stober Drives, Inc. Comtrac™ adjustable speed drive. Size: TD57—1058-K184W. Mfg. No. 1000345. Maximum input HP 5.0. Output 1504 lb.-in. at 74 RPM output, or 777 lb.-in. at 370 RPM. (2) 3 in. S-line fittings. Overall dimensions: L. 1 ft. 6-1/4 in. x W. 1 ft. 5-1/2 in. x H. 3 ft. 6-1/2 in.



