

Waukesha Positive Displacement Pump

Mfg: Waukesha

Model: 125

Stock No: RCJF1633K

Serial No:

Waukesha Positive Displacement Pump. Model: 125. Flow rate for new pump is 140 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump could handle your specific duty. Reliance Electric motor: 5 hp, 1745 rpm, 230/460 V, 12.4/6.2 A, 60 Hz, 3 phase. Motor drive: 1130 input hp, 1750 in rpm, 282 out rpm, 2441 torque, 6.2 ratio. Waukesha pumps feature ease of cleaning and disassembly without the use of tools. Rotors, body, and all parts in contact with the product are designed and manufactured for acceptability by USDA and 3-A sanitary standards. Rotors and body are constructed of 316 stainless steel. Typical applications include: milk, vegetables, fruits, flavorings, bakeries and meats. (2) 6-3/8 in. rotors. Inlet/outlet: (2) 3 in. ACME. Overall dimensions: 4 ft. 2 in. L x 1 ft. 10 in. W x 1 ft. 10 in. H.





