

Tri-Clover Positive Displacement Pump

Mfg: Tri-Clover

Model: PRED60-2-UC4-SL-S

Stock No: RCJF454.4

Serial No: TC004

Tri Clover Positive Displacement Pump. Model: PRED60-2-UC4-SL-S. S/N: TC004. Flow rate for new pump is 60 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. General Electric motor: serial no. 3560400330. 5 Hp, 1750 RPM, 230/460 V, 13/6.5 A, 60 Hz, 3 Phase. APG motor drive: 6.2 ratio, 11.3 input RPM, 2441 lbs. torque. (2) rotors: 5-3/4 in. L x 3-1/8 in. W. (1) 2 in. ACME inlet. (1) 2 in. ACME outlet. Overall dimensions: 4 ft. 2-1/2 in. L x 1 ft. 4 in. W x 1 ft. 7 in. H.





