

1992 Mueller Jacketed Tank- 3,500 Gallon

Mfg: Mueller

Model:

Stock No. RCPK502.40a

Serial No. P40926-1

1992 Mueller Jacketed Tank- 3,500 Gallon. S/N: P40926-1. MAWP: 200 psi @ 300 °F. MDMT: -20 °F @ 100 psi. Siemens Motor (mixer), 5 hp, 1725 rpm, 230/460 V, 12.8/6.4 amps. Chemineer motor drive, input: 5 hp, 1800 rpm, ratio: 21.4 to 1, output: 84 rpm. Mixer shaft: 2-1/2 in. dia. x 10 ft. L. with (2) 33 in. dia. propellers. (4) Baffles. Inner access ladder. Manway: 24 in. dia.. External liquid level indicator. Inlets: (1) 6 in. dia. 'S' line fitting, (2) 3 in. dia. 'S' line fittings, (4) 2 in. dia. 'S' line fittings, (2) 2 in. 'S' line fittings (jacket). Outlets: (2) 2 in. dia. 'S' line fittings (jacket), (1) 3 in. dia. 'S' line fitting (tank discharge). Overall dimensions: 90 in. dia. x 16 ft. 5 in. H.



