

Mueller Jacketed Portable Pressure Rated Processor- 200 Gallons

Mfg: Mueller

Model:

Stock No. RCPK510.18a

Serial No.:

Mueller Jacketed Portable Pressure Rated Processor- 200 Gallon. Heat transfer surface MAWP: 90 psi @ 302 °F. Internal mixing is possible through a 1-3/4 in. diameter x 29 in. H mixing shaft outfitted with (2) 37 in. dia. propellers offset at 45°. (1) 18 in. diameter infeed with flip-top cover. Baldor Industrial Motor, 2 hp, 1725 rpm, 208-230/460 V, 6.5-6.2/3.1 amps, 60 Hz, 3 phase. Electra Motor Drive, ratio: 50 to 1, output: 34.5 rpm. Inlets: (1) 1-1/2 in. dia. NPT (male, jacket). Outlets: (1) 1-1/2 in. dia. NPT (male, jacket), (1) 2 in. dia. 'S' line (tank discharge). Tank is mounted on (4) casters. Overall dimensions: 72 in. dia. x 61 in. L.





