

Cosmodyne Nitrogen Tank – 6500 Gallon

Mfg: Cosmodyne Mfg. Co.

Model:

Stock No: RCSC1553A.25

Serial No: 180

Cosmodyne Mfg. Co. Industrial Nitrogen Tank. S/N: 180. Max WP: 50 PSIG at +150°F to -320°F. Max design temp: +150°F at 50 PSIG. Shell: 0.141 in. Head: 0.181 in. Year: 1964. Work order: 45006. P/N: 2414500. Accessories include 24 fin vaporizer. Tank dimensions: 90 in. diameter x 19 ft. 6 in. straight wall. Estimated tank volume: 6,500 gallons. Skid dimensions: 91 in. W x 25 ft. L. Overall dimensions: 96 in. W x 27 ft. L x 10 ft. 5 in. H.





