

Waukesha 130 Positive Displacement Pump

Mfg: Waukesha Cherry-Burrell

Model: 130

Stock No.: RCSC359.50

Serial No.: 391058R1 05

SPX Waukesha Cherry-Burrell Positive Displacement Pump. Model: 130. S/N: 391058R1 05. Previously remanufactured. 3A Sanitary. Flow rate for new pump is 150 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Displacement per revolution: 0.254 gallon. Estimated flow rate with this gear drive is 73 GPM. SEW-Eurodrive gear drive ratio: 5.99 (final RPM 288). Baldor motor: 5 HP, 460V 6.6 amps, 1725 RPM, 60 Hz, 3-phase. Inlet/outlet ports: 3 in. dia I-line fittings. Overall dimensions 4 ft. 6 in. L x 1 ft. 6 in. W x 1 ft. 8 in. H.







