

Waukesha 130 Positive Displacement Pump

Mfg: Waukesha Cherry-Burrell

Model: 130

Stock No.: RCSC378.47a

Serial No.: 385489 05

Waukesha Cherry-Burrell Positive Displacement Pump. Model: 130. S/N: 385489 05. Also mentions serial: 05-93954R. 3A Sanitary. Flow rate for new pump is 150 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Displacement per revolution: 0.254 gallon. Estimated flow rate with this gear drive is 49 GPM. SEW-Eurodrive gear drive ratio: 9.06 (final RPM 193). Baldor Motor: 5 HP, 460V, 1750 RPM, 60 Hz, 3-phase. Inlet/outlet ports: 3 in. dia I-line fittings. Overall dimensions: 4 ft. 3 in. L x 1 ft. 5 in. W x 1 ft. 7 in. H. (ACN125-185)







