


# Capacity / WHP / VHP / NIPR



## Universal I Sanitary Pumps Model

# 015

Alloy 88 Rotors  
Standard Clearance  
Standard Port Size = 1.5"  
Displacement =  
0.0142 Gal/Rev

$$\text{BHP} = \text{WHP} + \text{VHP}$$




**Waukesha  
Cherry-Burrell**

611 Sugar Creek Road  
Delavan, WI 53115 USA  
Tel: 1-800-252-5200 or 262-728-1900  
Fax 1-800-252-5012 or 262-728-4904  
E-mail: [custserv@gowcb.com](mailto:custserv@gowcb.com)  
Web Site: <http://www.gowcb.com>

Effective Date: 2-15-2000  
Specifications subject  
to change without notice

Curve Number  
**95-07134**



	A	AO	B	CP	CP1	CP4	D	E	F	G	I	J	L	O	U	X	2X
IN	4.75	8.30	3.75	12.04	13.47	15.25	5.50	1.94	2.31	.41,SLOT	7.66	2.93	9.61	4.21	0.875	3.49	6.97
MM	121	211	95	306	342	387	140	49	59	10,SLOT	194	74	244	107	22	89	177

CP= Standard Cover, CP1= Jacketed Cover, CP4= Manual Vented Cover, Connection sizes for Jacketed Covers are ¾"-14 NPT on Models 006-UI to 030-UI, 1"-11-½ NPT on Models 060-UI and 130-UI.

Dimension 'X' and '2X' apply for Bevel Seat, "S"-Clamp, "Q"-Clamp, 15l and 14l fittings.