

Waukesha 220 Positive Displacement Pump

Mfg: Waukesha Cherry Burrell

Model: 220 U1

Stock No.: RCSC560.80

Serial No.: 2704594

SPX Waukesha Cherry-Burrell Positive Displacement Pump. Model: 220 U1. S/N: 2704594 R1. Date: Aug 2011. 3A Sanitary. Universal I series. Flow rate for new pump is 310 gpm with required horsepower and RPM. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Displacement per revolution: 0.522 gallon. Maximum pressure: 200 PSI. Estimated flow rate with this gear drive is 172 GPM. SEW-Eurodrive gear drive ratio: 5.31 (final RPM 329.5). Baldor Motor: 7.5 HP, 460V, 10 amps, 1750 RPM, 60 Hz, 3-phase. Inlet/outlet ports: 4 in. dia I-line fittings. Overall dimensions: 5 ft. L x 1 ft. 9 in. W x 2 ft. H. (ACN208-265)







