

Waukesha 220 Positive Displacement Pump

Mfg: Waukesha Cherry-Burrell

Model: 220

Stock No.: RCSC606.85

Serial No.: 392642R2 05

SPX Waukesha Cherry-Burrell Positive Displacement Pump. Model: 220. S/N: 392642R2 05. 3A Sanitary. Universal I series. Previously remanufactured. Flow rate for new pump is 310 gpm with required horsepower and RPM. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Displacement per revolution: 0.522 gallon. Maximum pressure: 200 PSI. Estimated flow rate with this gear drive is 177 GPM. SEW-Eurodrive gear drive ratio: 5.2 (final RPM 339). Baldor Motor: 15 HP, 460V, 18.5 amps, 1765 RPM, 60 Hz, 3-phase. Inlet/outlet ports: 4 in. dia I-line fittings. Overall dimensions 6 ft. 2 in. L x 1 ft. 10 in. W x 2 ft. 2 in. H. (ACN208-265)





