

Waukesha 220 Positive Displacement Pump

Mfg: Waukesha Cherry-Burrell

Model: 220 U1

Stock No.: RCSC622.105

Serial No.: 1000002704319

SPX Waukesha Cherry-Burrell Positive Displacement Pump. Model: 220 U1. S/N: 1000002704319. Date: 08/30/11. 3A Sanitary. Universal I series. Flow rate for new pump is 310 gpm with required horsepower and RPM. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Displacement per revolution: 0.522 gallon. Maximum pressure: 200 PSI. Estimated flow rate with this gear drive is 106 GPM. SEW-Eurodrive gear drive ratio: 8.59 (final RPM 204). Baldor Motor: 10 HP, 460V, 13 amps, 1760 RPM, 60 Hz, 3-phase. Inlet/outlet ports: 4 in. dia I-line fittings. Overall dimensions: 5 ft. 3 in. L x 1 ft. 6 in. W x 1 ft. 10 in. H. (ACN208-265)





