

Kettle Bridge-Mounted Bottom Scrape Agitator

Mfg:

Model:

Stock No. RFPM1604.4a

Serial No.:

Kettle Bridge-Mounted Bottom Scrape Agitator. Blade dimensions: 58 in. diameter x 28 in. H. Shaft: 1-1/2 in. diameter x 57 in. H. Bridge: 93 in. L x 8 in. W. Baffle: 5-3/4 in. W x 31 in. H. Choice of attaching (12) 7 in. L scrapers, or (6) 14 in. L scrapers. Sew-Eurodrive Motor, 5 hp. Sew-Eurodrive Gear Reducer, ratio: 61.26, input: 1700rpm, output: 28 rpm, torque: 3331 lb-in. Product inlet (on the bridge): 1-1/2 in. $\frac{1}{2}$ Spline, (2) 2 in. $\frac{1}{2}$ Spline. Overall dimensions: 99 in. L x 13 in. W x 65 in. H.



