

Sutorbilt Rotary Positive Blower

Mfg: Sutorbilt

Model: GACMDPA

Stock No: RGMB028

Serial No: U41939

Sutorbilt Rotary Positive Blower. Model: GACMDPA. S/N: U41939. Cat: 4MP. Max rpm: 3600. Motor: Baldor motor: 7 ½ hp, 1760 rpm, 230/460 V, 19.4/9.7 amps, 60 Hz, 3 phase. Outlets/Inlets: 3 in. dia. port. 2 ½ in. dia. port. Overall dimensions: 3 ft. 3 in. L x 1 ft. 11 in. W x 4 ft. 4 in. H.



