

**1996 RVS Recirculating Ammonia Tank - 54 in. Dia. x 10 ft. H**

**Mfg: RVS**



**Model:**

**Stock No: RGMB109**

**Serial No: 96903**

1996 RVS Recirculating Ammonia Tank. Serial No: 96903. Refrigerant: R-717. MAWP: 150 psi @ 300°F. MDMT: -50°F @ 60 psi. Inside straight-wall dimensions: 54 in. dia. x 10 ft. H. Radius: 2:1 elliptical ends. (2) Cornell pumps. Model: 2CB-5-4. (2) Baldor electric motor – 5 hp, 230/460 V, 3 phase. Inlet/Outlets: (1) 6 in. dia. ports, (1) 8 in. dia. port, (2) 2 ½ in. dia. ports, (3) 1 in. dia. ports. Overall dimensions: 6 ft. 9 in. L x 6 ft. 4 in. W x 18 ft.4 in. H.





SUPER-EFFICIENT INDUSTRIAL MOTOR

CAT. NO.	A15087G-55		CONNECTION LOW VOLTAGE
SPEC.	06F172W09		
FRAM	184CZ	H.P. 5	TE
SER.	F996 REFER DUTY		
VOLTS	230/460		HIGH VOLTAGE
AMPS	13.6/6.8		
R.P.M.	1760		LINE
HZ	60	PH 3	
SER. F.	1.15	DES B	CODE J
NEMA NOM. EFF.	90.2		HIGH VOLTAGE
RATING	40C AMB-CONT		
MFG. NO.	6207	FR BRG. 6205	

BALDOR ELECTRIC CO. FT. SMITH, AR.

**BALDOR**  
INDUSTRIAL MOTOR

THREE PHASE

CAT. NO.	A20295D-55		CONN L VOL
SPEC.	06F172W09		
FRAME	184CZ	SER. F996	8
H.P.	3	TE	
VOLTS	190/360		9
AMPS	11.7/5.5		
R.P.M.	1470		3
HZ	50	PH 3	
SER. F.	1.15	DES B	CODE J
NEMA NOM. EFF.	88	% P.F.	70%
RATING	40C AMB-CONT		HIGH VOLT LINE
	REFER DUTY		

CAT. NO.	A15087G-55		CONN L VOL
SPEC.	06F172W09		
FRAM	184CZ	H.P. 5	TE
SER.	F1096 REFER DUTY		
VOLTS	230/460		HIGH VOLTAGE
AMPS	13.6/6.8		
R.P.M.	1760		LINE
HZ	60	PH 3	
SER. F.	1.15	DES B	CODE J
NEMA NOM. EFF.	90.2		HIGH VOLTAGE
RATING	40C AMB-CONT		
MFG. NO.	6207	FR BRG. 6205	