

APV Crepaco R-Series Positive Displacement Pump

Mfg: APV Crepaco

Model: R3TS

Stock No: RGMP003.5

Serial No: 10050391-1-1104

APV Crepaco R-Series Positive Displacement Pump. Model: R3TS. S/N:10050391-1-1104. Flow rate for new pump is 40 gpm with required horsepower and pressure at 150 psig. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. APV Crepaco R-series pumps are known for their rugged, long-lasting, efficient performance. Every pump in the line has as standard a stainless steel body, resilient molded rotors, and a heavy cast iron gear case, which provides long-lasting, economical service over a wide range of products and applications, easy disassembly and cleanup, low maintenance. Leeson electric motor, 3 hp, 1770 rpm, 209-230/460 V, 8.2/4.1 amps, 60 Hz, 3 phase. Pump is belt driven. Driver pulley diameter: 3-1/4 in. Driven pulley diameter: 1 ft. 3-1/2 in. Ratio: 4.76. Final rpm: 372. Inlets/outlets: (2) 1-1/2 in. diameter S-Line fittings. Overall dimensions: 2 ft. 5-3/4 in L x 1 ft. 5 in. W x 1 ft. 8 in. H.







