

Vilter 8-Cylinder Reciprocating Compressor – 50 HP

Mfg: Vilter

Model: A12B448B

Stock No.: RGMP261

Serial No.: 22026

Vilter 8-Cylinder Reciprocating Compressor. Model/Size: A12B448B. S/N: 22026. Order No: D-96204-1. Refrigerant: R-717 (ammonia). Power supply: 240 V. Nominal capacity for the Vilter 448 series: 147.6 Tons of R-717 at 62.4 BHP with a 61.1°F condensing temp. and a 30°F suction temp. Displacement: 309 cfm (at maximum rpm). Maximum rpm: 1200. Maximum BHP with V-belt drive: 100 BHP. Maximum discharge pressure: 300 psi. Maximum discharge temperature: 300°F. Maximum suction pressure: 150 psi. Reliance Electric Motor, 50 hp, 1780 rpm, 230/460 V, 120/60 amps, 60 Hz, 3 phase. Drive pulley diameter: 11-1/2 in. Driven pulley diameter: 1 ft. 5 in. Pulley ratio: 0.67. Final rpm: 1200. Inlets: (1) 4 in. dia. refrigerant suction port. Outlets: (1) 3 in. dia. refrigerant discharge port. Overall dimensions: 6 ft. 4 in. L x 4 ft. 2 in. W x 5 ft. H. (ACN268-BC).





