

Vilter 6-Cylinder Reciprocating Compressor-75 HP

Mfg: Vilter

Model: 446

Stock No.: RGMP273

Serial No.: 4944ARC

Vilter 6-Cylinder Reciprocating Compressor – 75 HP. Model: 446. S/N: 4944ARC. Nominal capacity of the Vilter 446 series: 110.7 Tons of R-717 at 47.9 BHP with a 61.1°F condensing temp. and a 30°F suction temp. Displacement: 232 cfm (at maximum rpm). Maximum rpm: 1200. Maximum discharge pressure: 300 psig. Maximum discharge temperature: 300°F. Maximum BHP with V-belt drive: 100 BHP. Maximum suction pressure: 150 psi. Reliance Electric 75 hp Motor. Connection sizes: 4 in. suction and 3 in. discharge. (ACN197-BC).







