

Vilter 8-Cylinder Reciprocating Compressor – 50 HP

Mfg: Vilter

Model: 448

Stock No.: RGMP277

Serial No.: 4946ABRC

Vilter 8-Cylinder Reciprocating Compressor – 50 HP. Model: 448. S/N: 4946ABRC. Rated capacity for the Vilter 448 series: 147.6 Tons of R-717 at 62.4 BHP with a 61.1°F condensing temp. and a 30°F suction temp. Displacement: 309 cfm (at maximum rpm). Maximum rpm: 1200. Maximum BHP with V-belt drive: 100 BHP. Maximum discharge pressure: 300 psi. Maximum discharge temperature: 300°F. Maximum suction pressure: 150 psi. Connection sizes: 4 in. suction and 3 in. discharge. Reliance Electric 50 hp motor. (ACN268-BC)





