

2007 Raypak Raytherm Indoor Hydronic Boiler – 66 HP

Mfg: Raypak


Model: H3-0962

Stock No: RHOH03.3a

Serial No: 0704264389

2007 Raypak Raytherm Indoor Hydronic Boiler – 66 HP. Model: H3-0962. S/N: 0704264389. Natural Gas. Input BTUH: 962,700. Output BTUH: 788,600. H3: 2-stage firing. The Raytherm type H models have a 82% efficiency which, according to Raypak, is the highest of any atmospheric boiler. Max operating temp: 230°F. Gas port: 1 in. Water ports: 2.5 in. Flue diameter: 14 in. Approximate shipping weight: 705 lbs. Removed in running condition late 2013. Overall dimensions: 32.5 in. W x 52.375 in. L x 33.5 in. H.





	NATL. BD. 264389
	CERTIFIED BY RAYPAK, INC. OXNARD, CALIFORNIA
MAX W.P. WATER	160 PSI
BTU/HR INPUT	961,700
MFR SERIAL NO.	0704264389
MIN RELIEF VALVE CAP	789 LBS/HR
HEATING SURFACE	76 SQ. FT. BOILER
HEATING SURFACE	SQ. FT. EXTENDED
HEATING SURFACE	7.64 SQ. FT. WATERWALL
MAX WATER TEMP	250 ° F
BTU/HR OUTPUT	765,504
BTU/HR INPUT	961,700
MIN INPUT RATE	0 BTU/HR.
GAS	NAT
MODEL NO.	H3-0962
CATEGORY 1 BOILER	
ACCEPTED FOR USE CITY OF NEW YORK	
DEPARTMENT OF BUILDING	
CONTROL APPROVED	
MEAS. 497-54-E VOL. II	
AN. 221.13a-CSA 4.9a-2005	
LOW PRESSURE BOILER	
	FOR S OF UN T LARG MAX PERM SUPPLY PRES MIN. PERMISS PRESSURE PS INPUT ADJUST MANIFOLD PRES 120243 WHEN USED WITH ANSI Z39.1-1969 OR ANSI Z39.1-1982