

1997 Raypak Raytherm Indoor Hydronic Boiler – 66 HP

Mfg: Raypak


Model: H1-0962CBEAHHAA

Stock No: RHOH04.3a

Serial No: 9709142845

1997 Raypak Raytherm Indoor Hydronic Boiler – 66 HP. Model: H1-0962CBEAHHAA. S/N: 9709142845. Natural Gas. Input BTUH: 962,700. Output BTUH: 788,600. H1: mechanical modulation, set point 150°F-210°F. The Raytherm type H models have a 82% efficiency which, according to Raypak, is the highest of any atmospheric boiler. Max operating temp: 230°F. Gas port: 1 in. Water ports: 2.5 in. Flue diameter: 14 in. Approximate shipping weight: 705 lbs. Removed in running condition late 2013. Overall dimensions: 32.5 in. W x 52.375 in. L x 33.5 in. H.





	NATL. BD.	142845	H MIN CL F RIGH LEFT BACK TOP FOR SERV OF UNOBS A S
	CERTIFIED BY RAYPAK, INC. WESTLAKE VILLAGE CALIFORNIA		
MAX W.P. WATER	160	PS	
MIN RELIEF VALVE CAP		789	LBS/HR
HEATING SURFACE		78	SQ FT
MFR SERIAL NO	9709142845		
BTU/HR OUTPUT	788,594		
BTU/HR INPUT	961,700		BTU/HR
MIN INPUT RATE			
GAS	NAT		
MODEL NO.	H1.0962C-BEAHAAA		
			MAX. PERMISS SUPPLY PRESS MIN PERMISS PRESSURE FOR INPUT ADJUST MANIFOLD PRESS

Ohio | Department of Commerce

BOILER CERTIFICATE INSPECTION

made on 10/4/13 by inspector A. Minor
 (date) (name)

Steve Hsu
 (employed by) (employed by)