

2000 ABB Instrumentation Field Electro-Magnetic Flowmeter System

Mfg: ABB Instrumentation

Model: M03GA11A10R0000

Stock No. RLOL231.3a

Serial No. 00.W036821

2000 ABB Instrumentation Field Electro-Magnetic Flowmeter System. Model: M03GA11A10R0000. S/N: 00.W036821. Maximum pressure: 160 psig. Process temperature: 221 °F. Ambient temperature: 158 °F. Calibration factor 1: 0.8693. Calibration factor 2/3/4: 0/5/1.000. ABB Kent-Taylor Magmaster Transmitter, Model: MFE4ER100311 SEN/01W001754, S/N: 01W001754A, supply voltage: 95-240 VAC, frequency: 47-440 Hz. Inlets/outlets: (2) 3 in. dia. S-line fittings. Overall dimensions: 6-1/2 in. L x 3 in. W x 10 in. H. Overall dimensions (sensor): 12 in. L x 9 in. W x 14 in. H.



