

2003 ABB Instrumentation Field Electro-Magnetic Flowmeter System

Mfg: ABB Instrumentation

Model: M15GA18A10R1K03

Stock No. RLOL235.10a

Serial No. 03W016898

2003 ABB Instrumentation Field Electro-Magnetic Flowmeter System. Model: M15GA18A10R1K03. S/N: 03W016898. Maximum pressure: 250 psig. Process temperature: 221 °F. Ambient temperature: 158 °F. Calibration factor 1: 1.1130. Calibration factor 2/3/4: 0/5/1.000. ABB Kent-Taylor Magmaster Transmitter, supply voltage: 95-240 VAC, frequency: 47-440 Hz. Inlets/outlets: (2) 1-1/2 in. dia. fittings. Overall dimensions (transmitter): 6-1/2 in. L x 3 in. W x 10 in. H. Overall dimensions (sensor): 8 in. L x 7-1/2 in. W x 10-1/2 in. H.

