

2001 ABB Instrumentation Field Electro-Magnetic Flowmeter System

Mfg: ABB Instrumentation

Model: M02GA11A10R100A

Stock No. RLOL238.5

Serial No. V/88925/77/1

2001 ABB Instrumentation Field Electro-Magnetic Flowmeter System. Model: M02GA11A10R100A. S/N: V/88925/77/1. Maximum pressure: 250 psig. Process temperature: 221 °F. Ambient temperature: 158 °F. Calibration factor 1: 1.34590. Calibration factor 2/3/4: -25/9/1.000. ABB Kent-Taylor Magmaster Transmitter, Model: MFE4ER100311 SEN/01W013288, S/N: 01W013288A, supply voltage: 95-240 VAC, frequency: 47-440 Hz. Inlets/outlets: (2) 2 in. dia. fittings. Overall dimensions: 6-1/2 in. L x 3 in. W x 10 in. H. Overall dimensions (sensor): 8 in. L x 7 in. W x 11 in. H.



