

1999 ABB Instrumentation Field Electro-Magnetic Flowmeter System

Mfg: ABB Instrumentation

Model: M02GA18A10R0000

Stock No. RLOL239.4a

Serial No. 99W042046

1999 ABB Instrumentation Field Electro-Magnetic Flowmeter System. Model: M02GA18A10R0000. S/N: 99W042046. Maximum pressure: 250 psig. Process temperature: 140 °F. Ambient temperature: 158 °F. Calibration factor 1: 1.2948. Calibration factor 2/3/4: -22/5/1.0000. ABB Kent-Taylor Magmaster Transmitter, Model: M02G18A10R1003 SEN/V30003/9/1, S/N: A971401/1/8, supply voltage: 95-240 VAC, frequency: 47-440 Hz. Inlets/outlets: (2) 2 in. dia. fittings. Overall dimensions: 6-1/2 in. L x 3 in. W x 10 in. H. Overall dimensions (sensor): 8 in. L x 7 in. W x 11-1/2 in. H.





