

Tri-Clover Positive Displacement Pump

Mfg: Tri-Clover

Model: S-PR25-11/2M-UC405T-S

Stock No. RLOL265.6a

Serial No. S02818

Tri-Clover Positive Displacement Pump. Model: S-PR25-11/2M-UC405T-S, S/N: S02818. O-ring seals. Displacement per 100 revolutions: 8 gal. Capacity: 18 gpm @ 20 psi. Baldor Industrial Motor, 1 hp, 1140 rpm, 208-230/460 V, 3.6-3.4/1.7 amps, 60 Hz, 3 phase. Motor Drive, 229 rpm (final). Inlets/outlets: (2) 1-1/2 in. dia. Q-line fittings. Overall dimensions: 35 in. L x 15 in. W x 17 in. H.

