

## Pacemaker Motor- 15 HP

Mfg: Pacemaker

Model:

Stock No. RPAG1112.1a

Serial No.:

Pacemaker Motor- 15 HP. Motor specifications: 15 hp, 3515 rpm, 230/460 V, 38.0/19.0 amps, 60 Hz, 3 phase. Frame: X254T. Enclosure: TEFC. Type: P. Class: B. UL Listed No: U 768361. Class I Group D. Shaft diameter: 1-5/8 in. Overall dimensions: 23 in. L x 17-1/2 in. W x 15 in. H.

