

Brook Hansen Motor- 3 HP

Mfg: Brook Hansen

Model:

Stock No. RPAG1124J.

Serial No. F212673

Brook Hansen Motor- 3 HP. S/N: F212673. Explosion proof. Motor specifications: 3 hp, 1700 rpm, 230/460 V, 8.2/4.1 amps, 60 Hz, 3 phase. Frame: E184TC. Type: TEXP. Design: B. Insulation class: F. UL Listed. Class I Groups C & D. Class II Groups E, F, G. Shaft diameter: 1-1/8 in. Overall dimensions: 16 in. L x 11 in. W x 18 in. H.

