

Reliance Electric Duty Master A-C Motor- 3/4 HP

Mfg: Reliance

Model:

Stock No. RPAG1124M.

Serial No.:

Reliance Electric Duty Master A-C Motor- 3/4 HP. ID: B77U977/N-JB. Explosion proof. Motor specifications: 3/4 hp, 1725 rpm, 230/460 V, 3.0/1.5 amps, 60 Hz, 3 phase. Frame: HR56C. Type: P. Insulation class: B. Code: K. UL Listed No: FAG251709. Class I Groups C & D. Class II Groups F & G. Shaft diameter: 5/8 in. Overall dimensions: 11-1/2 in. L x 9 in. W x 8 in. H.

