

Reliance Electric Duty Master A-C Motor- 1/2 HP

Mfg: Reliance

Model:

Stock No. RPAG1124N.

Serial No.:

Reliance Electric Duty Master A-C Motor- 1/2 HP. ID: P56H2302M-ST. Explosion proof. Motor specifications: 1/2 hp, 1725 rpm, 208-230/460 V, 2.2-2.2/1.1 amps, 60 Hz, 3 phase. Frame: HP56. Type: P. Insulation class: B. Code: M. UL Listed No: F AA528148. Class I Group D. Class II Groups F & G. Shaft diameter: 5/8 in. Overall dimensions: 11-1/2 in. L x 9 in. W x 8 in. H.

