

### Hawker Siddeley Motor- 3.0 HP

Mfg: Hawker Siddeley

Model:

Stock No. RPAG1124S.

Serial No. E270144

Hawker Siddeley Motor- 3.0 HP. S/N: E270144. Explosion proof. Motor specifications: 3.0 hp, 1720 rpm, 460 V, 4.1 amps, 60 Hz, 3 phase. Frame: ES184TC. Type: TEFC. Code: K. Design: B. Insulation class: F. UL Listed No: AJ42660. Class I Groups C & D. Class II Groups E & F. Shaft diameter: 1-1/8 in. Overall dimensions: 16 in. L x 10 in. W x 16 in. H.

